

## 1000V INSULATED SCREWDRIVERS

## ▼ EIGHT-VE 1000V INSULATED SCREWDRIVER MODULES

## MOD.AYVE

- Comprising:
  - ● AY.3.5x100VE-4x100VE-5.5x125VE-6.5x150VE
  - ● APY.1X100VE-2X125VE
  - ● ADY.1X100VE-2X125VE
  - Tray PL.325.

**+ Compatible with the Facom modular storage system**





## VE 1000V INSULATED SCREWDRIVERS FOR SLOTTED HEADS

## ▼ AY.VE FOR SLOTTED HEADS

▷ ISO 2380, DIN 5264, NF E 74.352

Ref	A x E mm	L1 mm	l mm	L mm	ΔΔ g
AY.2.5X50VE	2,5 x 0,4	50	10	150	25
AY.2.5X75VE	2,5 x 0,4	75	10	175	25
AY.3X75VE	3,0 x 0,5	75	10	175	28
AY.3.5X75VE	3,5 x 0,6	75	10	175	35
AY.3.5X100VE	3,5 x 0,6	100	10	200	35
AY.4X100VE	4,0 x 0,8	100	10	200	35
AY.4X150VE	4,0 x 0,8	150	10	250	45
AY.5.5X125VE	5,5 x 1,0	125	15	225	70
AY.5.5X150VE	5,5 x 1,0	150	15	258	80
AY.5.5X200VE	5,5 x 1,0	200	15	319	85
AY.6.5X150VE	6,5 x 1,2	150	15	269	120
AY.6.5X200VE	6,5 x 1,5	200	15	319	170
AY.8X150VE	8,0 x 1,2	150	15	269	160
AY.8X175VE	8,0 x 1,2	175	15	294	170
AY.8X200VE	8,0 x 1,2	200	15	325	180
AY.10X150VE	10,0 x 1,6	150	15	269	205
AY.10X200VE	10,0 x 1,5	200	15	325	240
AY.12X250VE	12,0 x 2,0	250	15	375	360

**+ Safety**





## VE 1000V INSULATED SCREWDRIVERS FOR PHILLIPS® HEADS

## ▼ APY.VE FOR PHILLIPS® HEADS

▷ ISO 8764, NF E 74.355

Ref	Phillips® no.	L1 mm	L2 mm	Ø mm	L mm	ΔΔ g
APY.0X75VE	PH.0	75	10	4,0	175	35
APY.1X100VE	PH.1	100	18	5,0	208	60
APY.2X125VE	PH.2	125	18	6,5	244	100
APY.3X150VE	PH.3	150	18	8,0	275	160
APY.4X200VE	PH.4	200	18	10,0	325	240

**+ Safety**



## VE 1000V INSULATED SCREWDRIVERS FOR POZIDRIV® HEADS

## ▼ ADY.VE FOR POZIDRIV® HEADS

▷ ISO 8764, NF E 74.355

Ref	Pozidriv® no.	L1 mm	L2 mm	Ø mm	L mm	ΔΔ g
ADY.0X75VE	PZ.0	75	10	4,0	175	50
ADY.1X100VE	PZ.1	100	18	5,0	208	60
ADY.2X125VE	PZ.2	125	18	6,5	244	100
ADY.3X150VE	PZ.3	150	18	8,0	275	160

**+ Safety**

