



## 2 Double ended ring spanner set

Sets of the most used sizes.

Code	No.	Ø mm / Ø"AF	↔
6030070	2-6	6x7 8x9 10x11 12x13 14x15 16x17	700
6030580	2-8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	1400
6030740	2-10	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27	2250
6031120	2-100	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32	2200
6030900	2-12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x26 25x28 27x32	3500
6031040	2-120	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	3550
6031390	2-122 ISO	6x7 8x9 10x11 12x13 14x15 16x18 17x19 20x22 21x23 24x26 27x32 30x34	4000
6031470	2-8 A	1/4x5/16 5/16x3/8 7/16x1/2 9/16x5/8 19/32x11/16 3/4x25/32 13/16x7/8 15/16x1" AF	1800
6031630	2-10 A	1/4x5/16 5/16x3/8 7/16x1/2 9/16x5/8 19/32x11/16 3/4x25/32 13/16x7/8 15/16x1 1.1/16x1.1/4 1.1/8x1.5/16" AF	3250



## 4 Flat ring spanner straight pattern

Thin walls.

GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated, polished rings.

\* not standardised

Code	No.	Ø mm	L mm	a	b <sub>1</sub>	b <sub>2</sub>	↔
6052710	4 6x7	6 x 7	99	4,5	10,0	11,5	10
6053010	4 8x9	8 x 9	114	5,2	13,0	14,5	15
6053280	4 8x10	8 x 10	115	5,2	13,0	16,0	18
6053440	4 10x11	10 x 11	131	5,8	16,0	17,0	28
6053520	4 10x13	10 x 13	149	6,4	16,0	20,5	35
6053870	4 12x13	12 x 13	149	6,4	19,0	20,5	35
6054170	4 13x15*	13 x 15	161	7,2	20,5	23,0	50
6054250	4 14x15	14 x 15	161	7,2	21,5	23,0	50
6054330	4 13x17	13 x 17	167	7,8	20,5	25,5	60
6054410	4 14x17	14 x 17	169	7,8	21,5	25,5	60
6054680	4 16x17	16 x 17	169	7,8	24,5	25,5	65
6054760	4 17x19	17 x 19	186	8,5	25,5	28,0	80
6054840	4 18x19	18 x 19	186	8,5	27,0	28,0	80
6054920	4 19x22	19 x 22	209	9,4	28,0	32,5	115
6055060	4 20x22	20 x 22	209	9,4	29,5	32,5	120
6055140	4 19x24*	19 x 24	233	10,0	28,0	35,5	140
6055220	4 21x23	21 x 23	233	10,0	30,5	33,5	145
6055300	4 22x24	22 x 24	233	10,0	32,5	35,5	150
6055490	4 24x26	24 x 26	261	10,8	35,5	38,0	190
6055570	4 24x27	24 x 27	260	10,8	35,5	39,0	200
6055730	4 25x28	25 x 28	289	11,6	36,5	41,0	240
6055650	4 24x30	24 x 30	290	10,6	35,5	43,5	230
6055810	4 27x32	27 x 32	320	12,6	39,0	46,0	320
6056030	4 30x32	30 x 32	320	12,6	43,5	46,0	340
6056110	4 30x36	30 x 36	357	13,8	43,5	51,5	530
6056380	4 32x36	32 x 36	357	13,8	46,0	51,5	550
6056460	4 36x41	36 x 41	391	15,0	51,5	59,0	700
6056540	4 41x46	41 x 46	431	16,2	59,0	66,0	850
6056620	4 46x50	46 x 50	473	16,5	66,0	71,5	950

## 4 Flat ring spanner set

Code	No.	Ø mm	↔
6061700	4-8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	425
6062000	4-12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x26 25x28 27x32	1300
6062190	4-120	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	1350

## TX 4 Flat ring spanner for external TORX® drive

Straight shape. GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated, polished rings.

© = reg. Trademark of Camcar Textron Inc. USA

Code	No.	★ mm	L mm	a <sub>1</sub>	a <sub>2</sub>	b <sub>1</sub>	b <sub>2</sub>	↔
6059800	TX 4 E6xE8	5,74 x 7,52	110	5,0	6,0	9	11	25
6059900	TX 4 E10xE12	9,42 x 11,17	140	7,0	8,0	13	15	40
6060140	TX 4 E14xE18	12,9 x 16,7	180	8,5	9,5	17	21	80
6060220	TX 4 E20xE24	18,45 x 22,16	225	11,0	13,0	24	28	155

