

DORO CONGRESS - 200 Business Phone

APPLICATIONS


This uniquely designed business class telephone is ideally suited for all applications including business and government office environments.

Stylish in design, the Congress 200 provides a range of features such as the selectable message waiting indicator to suit all popular PABX applications.

The LCD displaying the dialled number, clock and call timer together with the headset port make this phone suitable for call centres, help desks and telemarketing environments.

The Congress 200 also includes 20 true one-touch memories and on-hook dialling for the busy executive and a one-way speakerphone for situations that require group listening.

Built to perform and highly durable, this sleek modern phone is an affordable and reliable alternative for any business.



DORO CONGRESS - 200 Business Phone

FEATURES

- Designer business class telephone
- LCD for displaying called number, clock and call timer
- One-way speakerphone for on hook dialling and group listening function
- Headset port with one button operation and LED indicator
- 20 true one-touch memories for frequently dialled numbers or PABX functions
- Data port for convenient computer connection and data transfer
- Message waiting lamp for voicemail indication
- Visual ring indicator for incoming calls
- Optional ring tone "Off"
- Hold key with LED and one-touch operation
- Pause button, # and * can be programmed for PABX functions
- Adjustable 5 position handset volume control
- Adjustable speaker volume control
- Hearing aid compatible
- Last number redial
- Three selectable ring melodies
- Selectable recall for specific PABX requirements
- Latching mute function to allow private enquiries
- Adjustable ringer volume (Hi/Med/Lo/Off)
- Extra long flexible handset cord for convenience
- Clear protective faceplate for company logo or information

Grey - Barcode number: 7319770 586618 - Order Part Number: 58661



Additional Technical Data

Height: 80mm
 Width: 175mm
 Depth: 215mm
 Weight: 654 grams

- Superior immunity to RF interference caused by mobile phones, DECT phones etc.
- Detachable modular handset cord (extending to 2.12 metres)
- Dual injection dial keys
- Selectable message wait settings (80-100v, 12vLR, 48vLR)
- Selectable recall (100/270/600ms)
- Tone/pulse selectable
- Modular line cord terminated with RJ45 plug plus converter plug

The above feature list is not exhaustive. Please consult the relevant product manual for a full list of features. Due to continued product improvement the product's features and specifications may vary slightly from the actual product shown.

