

2.4GHz HIGH RESOLUTION FREQUENCY COUNTER

Order Code: 127-0137



Features

- 8-digits green LED display with annunciators
- two-channel operating mode memory
- adjustable range and gate time
- high-safety design as per IEC 1010, cat. II

Specifications

- frequency range: 0.01Hz - 2.4GHz
- accuracy: time base error x frequency ± 1 digit
- gate time: 100 msec - 10 sec
- input characteristics:
 - channel A:
 - frequency range:
 - DC couple: 0.01Hz to 100HZ
 - AC couple: 100Hz to 50Mhz
 - sensitivity: 80mVrms
 - impedance: 1 Mohms
 - max. input voltage: 30V
 - channel B:
 - frequency range: from 50Mhz to 2.4Ghz
 - sensitivity: 50mVrms
 - impedance: 50 ohms
 - max. input voltage: 3V
- power supply: 110-220VAC $\pm 10\%$
- max. consumption: 5W
- dimensions: 270 x 215 x 100mm
- weight: 1.6kg