



FT02 Key features:

- Complete view of the card thanks to a large window
- Compact model, but working area of 190 x 290 mm
- Heating through forced convection
- Temperature control by microprocessor
- Digital display of different advises: temperature and time.
- Easy programmation for immediate control
- Safety: double window with air circulation, closing door access



Description	Item Code
Reflow oven, forced convection - FT 02	F31 114

Technical characteristics	FT 02
Working area	190 mm x 290 mm
Heater	2 levels
Quartz heating elements	2 x 1 KW
Temperature control	by microprocessor
Working temperature	up to 300°C
Thermic stabilisation time	about 3 minutes
External dimensions L x w x H	370 x 455 x 320 mm
Total power	2,2 KW
Net weight	16 Kg
Electrical supply	230 V- 50/60 Hz