

Skintop® Click / Click-R

(Farnell: Skintop Click)

Application

SKINTOP® Click, the most innovative cable entry system on the market for fastest mounting, with all the reliable attributes of the world renowned Skintop Cable Gland range. Click in – turn left – turn right – done. Skintop Click-R with reducing seal for smaller clamping ranges.

Gland component parts:

Gland body	special polyamide-based
Seal insert	elastomer

Technical features:

Connecting thread:	M 16x1,5 up to M 25x1,5
Functional thread:	multi-start trapezoidal thread
IP protection:	IP 68 -
Strain relief:	acc. to EN 50262
Temperature range:	-40°C up to + 100°C