



Suretech™ L90N

CE Simple Design



APPLICATIONS

Ideal for use in sterile pharmaceutical & medical device environments and production areas.

FEATURES AND BENEFITS

Sterile gamma irradiated powder free natural rubber latex glove

Long cuff eliminates unprotected gap between sleeve and glove

Inspected and packaged in a cleanroom environment, low extractable ions

Micro roughened surface for grip

Packaged in individually sealed film pair packs.

Size	Order code*
6	M10000363
6.5	M10000355
7	M10000359
7.5	M10000360
8	M10000361
8.5	M10000362
9	M10000356
Length 300 mm	
Thickness (double wall) 0.47 mm	

*While stocks last



Suretech™ L100N

CE Simple Design



APPLICATIONS

Ideal for use in all cleanroom environments such as pharmaceutical, medical device, semi-conductor & micro-electronics manufacturing.

FEATURES AND BENEFITS

Class 100 (F5209D) / ISO Class 5 compatible

Powder free natural rubber latex glove

Long cuff eliminates unprotected gap between sleeve and glove

Inspected and packaged in a cleanroom environment, low extractable ions

High tensile formulation with micro roughened finish gives excellent tear resistance

Uniquely bagged to minimise particulate contamination.

Size	Order code*
6	M03401
6.5	M03402
7	M03403
7.5	M03404
8	M03405
8.5	M03406
Length 310 mm	
Thickness (double wall) 0.47 mm	

*While stocks last



Suretech™ V75, Suretech™ V100

CE Simple Design



APPLICATIONS

Ideal for use in all cleanroom applications such as pharmaceutical, medical device.

FEATURES AND BENEFITS

Class 100/ISO Class 5 compatible (Suretech V75)

Class 10/ISO Class 4 compatible (Suretech V100)

Disposable, ambidextrous vinyl glove with extended cuff

Powder free

Good sensitivity and tear resistance.

Low extractable ions level

Multi layer packaging incorporating anti-static bag to minimise particulate contamination static build up.

Size	Order code
V75	
6.5 (S)	M08434
7.5 (M)	M08435
8.5 (L)	M08436
9.5 (XL)	M08437
Length 240 mm	
Thickness (double wall) 0.26 mm	
V100	
6.5 (S)	M08438
7.5 (M)	M08439
8.5 (L)	M08440
9.5 (XL)	M08441
Length 300 mm	
Thickness (double wall) 0.26 mm	