



D21716K-GB & LX

701W Single Speed Percussion Drill

Selling Proposition

- More powerful for heavy duty applications
- Soft grip to enhance user comfort
- Jampot construction design for added durability and ease of service
- High quality 13 mm keyed chuck for accuracy and durability
- Variable speed control with forward and reverse mode to suit different materials



Standard Equipment

- keyed chuck
- Chuck Key
- Multi-position side handle
- Heavy Duty carrying case
- Depth stop

Warranty Specifications

- 1 year free service contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Chuck Capacity	1.5-13 mm
Power Input	701 Watts
Power Output	360 Watts
Max Torque	12 Nm
No Load Speed	0-2600 rpm
Blows per Minute	0-44200 bpm
Max. Drilling Capacity [Wood]	30 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	16 mm
Spindle Thread	1/2" x 20 U.N.F

D21716K-GB & LX

Specifications	
Weight	1.8 kg
Length	280 mm
Height	185 mm
Hand/Arm Vibration - Metal	2.8 m/s ²
Hand/Arm Vibration - Impact	1.5 m/s ²