



Vinyl-insulated with copper sleeve

Applicable Wire mm ² (AWG#)	Part No.	Nominal Size DIN46245	Dimensions mm (in.)				Color	Tool No.	Qty/box
			ø d ₁	ø d ₂	l ₁	l ₂			
0.5 to 1.5 (20 to 16)	VDADF1.25-110A-8	B2.8-1	2.1 (.083)	3.4 (.134)	18.4 (.724)	13.4 (.528)	Red	JCH-1112	1,000
	VDADF1.25-110A-5	A2.8-1	2.1 (.083)	3.4 (.134)	18.4 (.724)	13.4 (.528)			
	VDADF1.25-187A-8	4.8-1	1.9 (.075)	3.4 (.134)	19.2 (.756)	14.2 (.559)			
1.1 to 2.5 (16 to 14)	VDADF2-187A-8	4.8-2.5	2.5 (.098)	4.0 (.157)	20.2 (.795)	14.2 (.559)	Blue	JCH-1112, JCH-1213	1,000
0.5 to 1.5 (20 to 16)	VDADF1.25-250A	6.3-1	1.8 (.071)	3.4 (.134)	21.0 (.827)	16.0 (.630)	Red	JCH-1112	1,000
1.1 to 2.5 (16 to 14)	VDADF2-250A	6.3-2.5	2.4 (.094)	4.0 (.157)	22.0 (.866)	16.0 (.630)	Blue	JCH-1213	1,000
2.6 to 6 (12 to 10)	VDADF5.5-250A	6.3-6	3.7 (.146)	5.8 (.228)	23.0 (.906)	17.0 (.669)	Yellow	JCH-1213	500

Note: 1) Contact J.S.T. Europe N.V., Belgium for the above tools.
 2) Delivery lead times may vary depending on the product. Contact JST for details.