

# GP Batteries

Data Sheet

Model No.: GP14AU

## NO MERCURY ADDED

Description : Mercury Free Alkaline Manganese Battery, C Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions :  $\varnothing 26.2$  mm x 50.0 mm

Terminals : Protruded positive(+) and flat negative(-) contacts

Jacket : Foil jacket


Applications : All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, lighting & torches, portable fans.

Warranty Period : 36 months

Average Weight : 60g


### Typical Service Life:


| Discharge Resistance | Discharge Condition | End Point Voltage | Service Life |
|----------------------|---------------------|-------------------|--------------|
| 3.9 Ohms             | 24 Hrs/ Day         | 0.9V              | 18 Hrs       |



### Cross References:

| GP   | JIS  | IEC  | Eveready | Duracell | Varta |
|------|------|------|----------|----------|-------|
| 14AU | LR14 | LR14 | E39      | MN1400   | 4014  |



 Member  
Gold Peak Group

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

0602011488