


PT-9700PC

TZ-Tape



PC connectable Desktop Labelling machine



Copy

Catalogue Spec

- Print Tested to the extreme labels up to 36mm
- Fast Print Speed
- Comes with Free Tape and Power Adaptor
- Built in automatic cutter enables accurate tape length

PT-9700PC

Colour: Light Grey and Pearl White

Tape widths: Machine accepts current range of HG & TZ Tapes:

- 3.5mm to 36mm (TZ Tapes)
- *12mm to 36mm (HG Tapes)

Tape inclusion:

HG-261 36mm Black on white (8 Metre length) tape

Keyboard: N/A

Hardware

PRINTING	PT-9700PC
Dimensions	116mm(W) x 192.7mm(D) x 140mm(H)
Design	Cube
Weight	1.57kg
Housing Color	Light Gray & Pearl White
Keyboard	Not available
Number of Keys	2(Power On/Off, Feed and Cut)
Tape Cutter	Auto Full Cutter, Auto Half Cutter (Laminated tape only)
Power	AC adaptor (AD9100ES) (Enclosed)
Display	Not available
Panel LED lamp	Red For Error status Green For Ready status
USB A lamp	None
LAN LED lamp	None
Attachments	CD-ROM [P-touch Editor 5.0 for Windows, P-touch Editor 5.0 for Mac, Printer Driver, Software User's Guide, P-touch Template tools, ESC/P tools] User's guide TZ tape(24mm Black on White Laminated Tape)
Tape Cartridge	TZ Tape, HG Tape
Tape width variations	TZ 3.5-36mm, HG Tape 6-36
Print Method	Thermal transfer
Max. Print Height	27.1mm

Print Speed(tentative)	Maximum. 20mm / sec (For TZ/AL tape) Maximum. 52mm / sec (For high-speed mode of HG tape only) Maximum. 80mm / sec (For high-speed draft mode of HG tape only)
Print Head	360 dpi/384 dots
Print resolution	360dpi(TZ / AL tape) 360dpi x 720dpi(For high resolution mode of HG tape only) 360dpi x 180dpi(For high speed mode of HG tape only)
Cutter Sensor	Yes
Tape End Sensor	Yes
Cover Open Sensor	Yes
Tape sensor	Yes
USB Function Interface	USB2.0 Full Speed
RS-232C Interface	Yes
USB Host Interface	N/A
LAN Interface	N/A
ESC/P Printing	Yes
USB ID switching	N/A

Temperature	10°C to 35°C
Humidity	20% to 80%