



Sample photo

**Order symbol:** PC 17/16-LFC3  
**Product nbr:** 7520204

**EAN:** 6418074010247

**Description:** Enclosure, PC  
**Remarks:** Low base, front plate frame

**Including:** Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:				Rating:	
	L	W	H		
mm:	160	166	102	<b>Ingress Protection (EN 60529):</b> IP 65	
inch:	6.3	6.5	4	<b>Impact Resistance (EN 50102):</b> IK 08/07	
Materials:				<b>Electrical insulation:</b> Totally insulated	
<b>Material:</b>	PC			<b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes	
<b>Base colour:</b>	RAL 7035			<b>UV resistance:</b> UL 508	
<b>Gasket material:</b>	EPDM and Polyurethane			<b>Flammability Rating (UL 746 C 5):</b> UL 94 5V	
Temperatures:				<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960	
<b>Short term:</b>	-40 ... 120 °C			<b>NEMA Class:</b> NEMA 1, 3, 3R, 4X, 12, 13	
<b>Continuous:</b>	-40 ... 80 °C			Certificates:	
<b>Short term:</b>	-40 ... 250 °F			<b>Underwriters Laboratories</b>	
<b>Continuous:</b>	-40 ... 175 °F			<b>Fimko</b>	
Accessories:				<b>Europe EN 50298 1998</b>	
MP 17/16	Mounting plate			<b>UL Canada</b>	
FP 17/16	Front plate			<b>Gost R</b>	

