



Sample photo

Order symbol: PC 17/16-FC3
Product nbr: 7520280

EAN: 6418074010254

Description: Enclosure, PC
Remarks: Front plate frame

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:				Rating:	
	L	W	H		
mm:	160	166	115	Ingress Protection (EN 60529): IP 65	
inch:	6.3	6.5	4.5	Impact Resistance (EN 50102): IK 08/07	
Materials:				Electrical insulation: Totally insulated	
Material:	PC			Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:	RAL 7035			UV resistance: UL 508	
Gasket material:	EPDM and Polyurethane			Flammability Rating (UL 746 C 5): UL 94 V5	
Temperatures:				Glow Wire Test (IEC 695-2-1) °C: 960	
Short term:	-40 ... 120 °C			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13	
Continuous:	-40 ... 80 °C			Certificates:	
Short term:	-40 ... 250 °F			Underwriters Laboratories	
Continuous:	-40 ... 175 °F			Fimko	
Accessories:				Europe EN 50298 1998	
MP 17/16	Mounting plate			UL Canada	
FP 17/16	Front plate			Gost R	

