

# ▶ PRO-LITE

## Product Data Specification

### PRO-LITE - 20 LED GU10 PAR16 240V

#### DESCRIPTION





The LED GU10 is a like for like size replacement for the 240V GU10 lamp. Available in a wide range of colours including a colour changing model, the lamps have an ultra long life of 30,000 hours.

#### APPLICATIONS

- Domestic & Commercial
- Areas of difficult access

#### FEATURES

- 30,000 hr average lamp life
- Low maintenance
- 240V input with GU10 cap
- Very low heat output
- Clear lens
- Ease of installation
- RoHS compliant



#### TECHNICAL SPECIFICATION

| Product Code     | Wattage | Colour             | Number of LEDs | LED Angle |
|------------------|---------|--------------------|----------------|-----------|
| GU10/LED/BLUE    | 1.8     | Blue               | 20             | 15        |
| GU10/LED/GREEN   | 1.8     | Green              | 20             | 15        |
| GU10/LED/MAGENTA | 1.8     | Magenta            | 20             | 15        |
| GU10/LED/ORANGE  | 1.8     | Orange             | 20             | 15        |
| GU10/LED/RED     | 1.8     | Red                | 20             | 15        |
| GU10/LED/CHANGER | 1.8     | RGB Colour Changer | 18             | 15        |
| GU10/LED/UV      | 1.8     | Ultra Violet       | 20             | 15        |
| GU10/LED/WHITE   | 1.8     | White              | 20             | 15        |