

▶ PRO-LITE

Product Data Specification


PRO-LITE - 35-105VA Electronic Transformer

FEATURES

- Dimmable
- Highly efficient
- EMC Approved
- Short circuit, over-load and surge protected
- Thermal cut-off
- RoHS compliant
- Ambient temperature Ta. Max: 40°C
- Case temperature Tc. Max: 65°C

TESTED ACCORDING TO

- EN61347-2-2:2001
- EN61347-1:2001
- EN55015:2000/A1:2001
- EN61547:1995/A1:2000
- EN61000-3-3:2000
- EN61000-3-3:1995/+A1:2001



TECHNICAL SPECIFICATION

Product Code	Input Voltage	Input Current	Output Voltage	Usage	IP Rating
TRANS-105VA/PROL	220-240V 50Hz	0.40A	11.6V	Indoor	IP20

