

**Spiralbohrer-Magazin DIN 338 Typ N
HSS-G Co 5 geschliffen in Stahlblechkassette - schwarz**

19 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS Co 5
mit Kreuzanschliff
Ø 1,0 - 10,0 mm x 0,5 mm steigend

Art.-Nr. A 215 319

25 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS Co 5
mit Kreuzanschliff
Ø 1,0 - 13,0 mm x 0,5 mm steigend

Art.-Nr. A 215 325

NETTO-PREISE

A 215 325

€



A 215 319

€

**Spiralbohrer-Magazin DIN 338 Typ N HSS-G
geschliffen in Stahlblechkassette - schwarz**

19 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS-G
mit Kreuzanschliff
Ø 1,0 - 10,0 mm x 0,5 mm steigend

Art.-Nr. A 214 319

25 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS-G
mit Kreuzanschliff
Ø 1,0 - 13,0 mm x 0,5 mm steigend

Art.-Nr. A 214 325

A 214 325

€



A 214 319

€

NETTO-PREISE

**Spiralbohrer-Magazin DIN 338 Typ N HSS-R mit blankem
Kegelmantelanschliff in Stahlblechkassette - schwarz**

19 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS-R
mit blankem Kegelmantelanschliff
Ø 1,0 - 10,0 mm x 0,5 mm steigend

Art.-Nr. A 205 319

25 tlg. Spiralbohrer-Satz DIN 338 Typ N HSS-R
mit blankem Kegelmantelanschliff
Ø 1,0 - 13,0 mm x 0,5 mm steigend

Art.-Nr. A 205 325

A 205 319

€



A 205 325

€

Twist drill magazine DIN 338 type N HSS Co 5 ground with split point in steel case - black

19-piece set of twist drills DIN 338 HSS Co 5 with split point
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

Art. no. A 215 319

25-piece set of twist drills DIN 338 HSS Co 5 with split point
Ø 1,0 mm up to 13,0 mm in increments 0,5 mm

Art. no. A 215 325

A 215 325
34,60 €



NET-PRICE

A 215 319
15,70 €

Twist drill magazine DIN 338 type N HSS ground with split point in steel case - black

19-piece set of twist drills DIN 338 HSS with split point
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

Art. no. A 214 319

25-piece set of twist drills DIN 338 HSS with split point
Ø 1,0 mm up to 13,0 mm in increments 0,5 mm

Art. no. A 214 325

A 214 325
17,80 €



A 214 319
8,30 €

A 205 325
9,30 €

NET-PRICE

Twist drill magazine DIN 338 type N HSS rolled with bright helical point in steel case - black

19-piece set of twist drills DIN 338 HSS rolled with bright helical point
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

Art. no. A 205 319

25-piece set of twist drills DIN 338 HSS rolled with bright helical point
Ø 1,0 mm up to 13,0 mm in increments 0,5 mm

Art. no. A 205 325

A 205 319
4,50 €

