



ALAN BUTCHER COMPONENTS LTD



Alan Butcher Components Ltd
 Unit 1 Beechwood
 Clump Farm Industrial Estate
 Tin Pot Lane Blandford
 Dorset DT11 7TD

Telephone 01258 456360
 Facsimile 01258 459194
 sales@abcomponents.co.uk
 www.abcomponents.co.uk

ABI-004-RC SPECIFICATION SHEET

Features:

- Colour: Black
- Housing Material: ABS
- Panel or Base Flange Mounted



All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABI-004-RC – Piezo Indicator
Rated Voltage	12VDC
Operating Voltage	1.5 ~ 16VDC
Rated Current at rated voltage	15mA
Min Sound Output at 30cm, at rated voltage	95dB
Resonant Frequency	3500±500Hz
Tone	Continuous
Operating Temperature	-20 ~ +60°C
Storage Temperature	-30 ~ +70°C
Lead Wire	UL1007 AWG26
Weight	15g

Value applying rated voltage (DC)

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

