



## MAB-06B-SA

### Specifications

Dimensions	Dia 7.7 x 3 (mm)
Operating Voltage	1.1 ~ 10 V
Sensitivity	-42 +/- 3 dB
Directivity	Omni-directional
Current Consumption	500 $\mu$ A (max)
Signal to Noise	60 dB (min)
Weight	0.3 Grams

