



MAA-03A-L60

Specifications

Dimensions	Dia 3 x 1.5 (mm)
Operating Voltage	1. ~ 10 V
Sensitivity	-44 +/- 3 dB
Directivity	Omni-directional
Current Consumption	500 μ A (max)
Signal to Noise	55 dB (min)
Weight	0.5 Grams

