

Säbelsägen-Satz mit Universal-Handgriff im Kunststoffkoffer

6 tlg. Säbelsägen-Satz inkl. Handgriff

- Einfacher Werkzeugwechsel durch Zugmechanismus
- Sägen, schneiden und schrauben mit einem Werkzeug möglich
- Drehmoment bis 28 Nm von Hand

RUKO 8908 Säbelsäge HSS-Bimetall (**Bosch Nr. S 922 EF**)
für dünne Metallbleche
150,0 x 18,0 x 0,9 mm Zahnteilung 1,4 mm / 18 tpi

RUKO 8915 Säbelsäge HSS-Bimetall (**Bosch Nr. S 922 BF**)
für starke Metallbleche, Edelstahlbleche, Rohre und Profile
150,0 x 18,0 x 0,9 mm Zahnteilung 1,8 mm / 14 tpi

RUKO 8909 Säbelsäge HSS-Bimetall (**Bosch Nr. S 1022 HF**)
für Holz, Metallbleche und Aluprofile
200,0 x 18,0 x 0,9 mm Zahnteilung 2,5 mm / 10 tpi

RUKO 8924 Säbelsäge HCS (**Bosch Nr. S 644 D**)
für Sperrholz, Spanplatten und Kunststoffe
150,0 x 18,0 x 1,25 mm Zahnteilung 4,2 mm / 6 tpi

RUKO 8905 Säbelsäge HCS (**Bosch Nr. S 617 K**)
für Holz aller Art, Äste
150,0 x 18,0 x 1,25 mm Zahnteilung 8,5 mm / 3 tpi

Art.-Nr. 331 100



Reciprocating blade set with universal handle in plastic case

Reciprocating blade set with universal handle 6 pcs.

- Easy tool change through pull mechanism
- Sawing, cutting and screwing possible with just one tool
- Turning moment manually up to 28 Nm

RUKO 8908 Reciprocating blade HSS bimetal (**Bosch no. S 922 EF**)
for thin sheeting
150,0 x 18,0 x 0,9 mm Tooth spacing 1,4 mm / 18 tpi

RUKO 8915 Reciprocating blade HSS bimetal (**Bosch no. S 922 BF**)
for thick sheeting, stainless steel sheet metal, pipes and profiles
150,0 x 18,0 x 0,9 mm Tooth spacing 1,8 mm / 14 tpi

RUKO 8909 Reciprocating blade HSS bimetal (**Bosch no. S 1022 HF**)
for wood, metal sheeting and aluminium profiles
200,0 x 18,0 x 0,9 mm Tooth spacing 2,5 mm / 10 tpi

RUKO 8924 Reciprocating blade HCS (**Bosch no. S 644 D**)
for plywood, chipboard und plastics
150,0 x 18,0 x 1,25 mm Tooth spacing 4,2 mm / 6 tpi

RUKO 8905 Reciprocating blade HCS (**Bosch no. S 617 K**)
for every kind of wood, pruning
150,0 x 18,0 x 1,25 mm Tooth spacing 8,5 mm / 3 tpi

Art. no. 331 100

25,90 €



NEW