

NOZZLE THERMOCOUPLE for up to 350°C

A type J or K thermocouple housed in a threaded bolt

- 1 Grounded tip for fast response
- 2 Adjustable insertion
- 3 M6 x 1mm threaded stainless steel bolt
- 4 2m glassfibre stainless steel braided extension lead, 7/0.2mm

Dimensions & Codes

	Farnell code	LAB code
Type J, 2m lead	8598045	FN-J-2M
Type K, 2m lead	8598053	FN-K-2M



Data Ref: FAR 38