

MINIATURE CABLE TIDY WITH FINE WIRE THERMOCOUPLE


- 1 Complete precision thermocouple assembly, Class 1
- 2 High sensitivity, fast response
- 3 2m wire stored on stem with fitted mini-plug
- 4 Ideal for test & measurement

Specifications

Construction:	Stainless steel storage stem with wire strain relief mounted on miniature plug
Sensor type:	Type K & T thermocouples, 2m length.
Wire type:	Class 1 wire for high accuracy PFA insulated wire, twin twist 1/0.2 and flat pair 1/0.315mm conductors.
Temperature rating:	220°C continuous Plug PFA 250°C

Dimensions & Codes

	Farnell code	LAB code
Type K, 2m twin twist, 1/0.2mm	8598118	CT-Z2-PFA-K-2
Type K, 2m flat pair, 1/0.315mm	8598126	CT-Z4-PFA-K-2
Type T, 2m twin twist, 1/0.2mm	8598134	CT-Z2-PFA-T-2
Type T, 2m flat pair, 1/0.315mm	8598142	CT-Z4-PFA-T-2



Data Ref: FAR 42