

WELDED TIP THERMOCOUPLES

- 1 Fast response, exposed junction
- 2 Thermocouple types J,K,T & N to IEC 60584
- 3 PTFE / PFA insulated wires, class 1
- 4 Rated -75°C to $+250^{\circ}\text{C}$
- 5 Ideal for test & development applications

Pack of 5

PTFE x 2m twin twist 1/0.2mm

Dimensions & Codes

	Farnell code	LAB code
Type K tails	8598150	Z2-K-2x5
Type T tails	8598169	Z2-T-2x5
Type N tails	8598177	Z2-N-2x5
Type K mini-plug	8598185	Z2-K-2-MPx5
Type T mini-plug	8598193	Z2-T-2-MPx5
Type N mini-plug	8598207	Z2-N-2-MPx5
Type J mini-plug	8598215	Z2-J-2-MPx5

Pack of 5

PTFE x 1m twin twist 1/0.2mm

Dimensions & Codes

	Farnell code	LAB code
Type K tails	8598223	Z2-K-1x5
Type T tails	8598231	Z2-T-1x5



Data Ref: FAR 43

FINE WIRE WELDED TIP THERMOCOUPLES

- 1 High sensitivity, exposed junction
- 2 Thermocouple types K & T to IEC 60584
- 3 PFA insulated wires, class 1
- 4 Rated -75°C to $+250^{\circ}\text{C}$
- 5 Ideal for test & development applications

Pack of 5

PFA x 1m, singles 1/0.08mm

Dimensions & Codes

Farnell code	LAB code
--------------	----------

Type K tails
Type T tails

8598240
8598258

Z0-PFA-K-1x5
Z0-PFA-T-1x5



Data Ref: FAR 43 A