
Item no.: 231-306/026-000
Product description: FEMALE PLUG; 6 POLE; PIN SPACING 5.08 MM / 0.2 IN;
WITH CODIG FINGERS; WITH INTEGRATED FIXING
FLANGES; CAGE CLAMP®CONNECTION



Packing unit 50 pieces

Pin spacing from	5,08 mm
Pin spacing from	0,2 in
pole count	6
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Voltage CSA	300 V
Current CSA	15 A
Voltage UL	300 V
Voltage UL	600 V
Current UL	15 A
Weight	10,98 g
Color	orange
No. of connection Points	6
No. of potentials	6
Height	14,3 mm



Width	31,98 mm
Width	1,259 in
Depth	26,45 mm
Depth	1,041 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-306/026-000	BV	11915/A0	400	16	2,5
231-306/026-000	CSA	154112-1466354	300	15	22-12
231-306/026-000	DEMKO	88126	250		2,5
231-306/026-000	KEMA	98.2486.01	250	16	
231-306/026-000	KR	HMB05880-EL003	250/400/600	12/16	2,5
231-306/026-000	NEMKO	P94101840	250		2,5
231-306/026-000	UL	E45171	600	15	22-12
231-306/026-000	UL	E45172	300	15	22-12
231-306/026-000	VDE	5675ÜGBI.2	250	16	2,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected