

Product Description



Application

The innovative CLICK system now also available with additional bending protection for flexible cables. Cables for electrical appliances and machinery, which are moved under normal use, must be protected against excessive bending, as required in accordance with VDE 0730. Safety feature for flexible cables used in e. g.:

- Hand-held equipment
- Flexing machine parts
- Apparatus engineering
- Light and sound applications
- Robotics industry

Advantage

- Up to 70% time saving due to innovative CLICK system
- Simple, free assembly in any position
- Fewer parts, counter nut no longer needed
- Captive
- No thread required
- protected against vibration
- Maximum quality
- Strain relief in acc. with EN 50262
- IP 68, hermetically sealed
- Reliable bending protection for cable conservation and functional reliability

Note

- Disassembly tool contained in the delivery scope



Technical Data

Approvals

VDE approval for sizes M12 and M32 in preparation

Colour delivered

RAL 7001 silver-grey RAL 7035 light grey RAL 9005 black / UV resistant

Material

Body: special polyamide Seal: special elastomer

Degree of protection

IP 68 - 5 bar

Range of temperature

-20°C up to +100°C

Article List

Part number	Part designation / size	Clamping range ØF mm	M (hole mm)	Overall length C mm	Thread length D mm	SW1 / SW2 mm	S (wall thickness mm)	Pieces / VPE
SKINTOP® CLICK BS light grey								
53112932	CLICK BS 12	3,5 - 7	12,3 (-0,2)	74	8	15 / 18	1 - 4	50
53112888	CLICK BS 16	5 - 9	16,3 (-0,2)	94	8	19 / 22	1 - 4	50
53112889	CLICK BS 20	7 - 13	20,3 (-0,2)	108	8	19 / 22	1 - 4	25
53112890	CLICK BS 25	9 - 17	25,3 (-0,2)	127	8	30 / 34	1 - 4	25
53112933	CLICK BS 32	11 - 21	32,3 (-0,2)	155	8	36 / 40	1 - 4	25
SKINTOP® CLICK BS silver-grey								
53112934	CLICK BS 12	3,5 - 7		74	8	15 / 18	1 - 4	50
53112906	CLICK BS 16	5 - 9	16,3 (-0,2)	94	8	19 / 22	1 - 4	50
53112907	CLICK BS 20	7 - 13	20,3 (-0,2)	108	8	19 / 22	1 - 4	25
53112908	CLICK BS 25	9 - 17	25,3 (-0,2)	127	8	30 / 34	1 - 4	25
53112935	CLICK BS 32	11 - 21	32,3 (-0,2)	155	8	36 / 40	1 - 4	25
SKINTOP® CLICK BS black								
53112936	CLICK BS 12	3,5 - 7		74	8	15 / 18	1 - 4	50



53112909	CLICK BS 16	5 - 9	16,3 (-0,2)	94	8	19 / 22	1 - 4	50
53112911	CLICK BS 20	7 - 13	20,3 (-0,2)	108	8	19 / 22	1 - 4	25
53112912	CLICK BS 25	9 - 17	25,3 (-0,2)	127	8	30 / 34	1 - 4	25
53112937	CLICK BS 32	11 - 21	32,3 (-0,2)	155	8	36 / 40	1 - 4	25