

### Product Description



### Application

The most innovative cable insertion system on the market for very fast, highly flexible assembly with all the proven properties of our SKINTOP® cable glands in use world-wide. Simply click in - turn to left - turn to right - finished. Result: fixed, centred, strain relieved and maximum protection class in seconds.

Developed especially for:

- Manufacturing of control cabinets
- Measurement, control and electrical applications
- Automation technology
- Plant, apparatus construction
- Control system construction
- Solar applications

### Advantage

- Up to 70% time saving due to innovative CLICK system
- Simple, free assembly in any position
- Fewer parts, counter nut no longer needed
- Captive
- No thread required
- protected against vibration
- Maximum quality
- Strain relief in acc. with EN 50262
- IP 68, hermetically sealed

### Note

- Disassembly tool contained in the delivery scope



Technical Data

Approvals

VDE approval for sizes M12 and M32 in preparation

Colour delivered

RAL 7001 silver-grey RAL 7035 light grey RAL 9005 black / UV resistant

Material

Body: special polyamide Seal: special elastomer

Degree of protection

IP 68 - 5 bar

Range of temperature

-20°C up to +100°C

Article List

Part number	Part designation / size	Clamping range ØF mm	M (hole mm)	Overall length C mm	Thread length D mm	SW1 / SW2 mm	S (wall thickness mm)	Pieces / VPE
SKINTOP® CLICK light grey								
53112692	CLICK 12	3,5 - 7	12,3 (-0,2)	40	8	15 / 18	1 - 4	50
53112686	CLICK 16	5 - 9	16,3 (-0,2)	42	8	19 / 22	1 - 4	50
53112687	CLICK 20	7 - 13	20,3 (-0,2)	45,5	8	25 / 27	1 - 4	25
53112688	CLICK 25	9 - 17	25,3 (-0,2)	48,5	8	30 / 34	1 - 4	25
53112694	CLICK 32	11 - 21	32,3 (-0,2)	55	8	36 / 40	1 - 4	25
SKINTOP® CLICK silver-grey								
53112921	CLICK 12	3,5 - 7	12,3 (-0,2)	40	8	15 / 18	1 - 4	50
53112876	CLICK 16	5 - 9	16,3 (-0,2)	42	8	19 / 22	1 - 4	50
53112877	CLICK 20	7 - 13	20,3 (-0,2)	45,5	8	25 / 27	1 - 4	25
53112878	CLICK 25	9 - 17	25,3 (-0,2)	48,5	8	30 / 34	1 - 4	25
53112922	CLICK 32	11 - 21	32,3 (-0,2)	55	8	36 / 40	1 - 4	25
SKINTOP® CLICK black								



53112923	CLICK 12	3,5 - 7	12,3 (-0,2)	40	8	15 / 18	1 - 4	50
53112882	CLICK 16	5 - 9	16,3 (-0,2)	42	8	19 / 22	1 - 4	50
53112883	CLICK 20	7 - 13	20,3 (-0,2)	45,5	8	25 / 27	1 - 4	25
53112884	CLICK 25	9 - 17	25,3 (-0,2)	48,5	8	30 / 34	1 - 4	25
53112924	CLICK 32	11 - 21	32,3 (-0,2)	55	8	36 / 40	1 - 4	25