

Type
Q 4
56 x 40 x 23 mm



Description

IP 20 junction box, according to VDE 0711, $U_i=400\text{ V}$,
4 entries with strain relief,
2 entries can be reached from the top, strain relief clamp
for pendant lights, with external fixing lugs


New

Q4 – empty, grey

Order No. **Packing Qty**

334 904 01 25

Mini 25
89 x 43 x 37 mm



IP 55 junction box according to E DIN IEC 60998-2-5, $U_i=400\text{ V}$,
10 entries, 2 bottom entries,
suitable for cramped installation environments
such as suspended ceilings and cable conduits,
complete with piercing tool and seals,
external fixing lugs

Mini 25 – empty, grey,
for VDE approved single terminals

310 908 01 40


Mini 25 – 2,5², grey,
3 interlockable screw terminals 2,5mm²

310 408 01 40

Mini 25 - SL, grey,
3 screwless terminals 5 x 1,0-2,5 mm²

310 808 01 40

Sd 7
75 x 75 x 37 mm



IP 55 junction box according to E DIN IEC 60998-2-5, $U_i=400\text{ V}$,
7 entries, 3 bottom entries,
complete with piercing tool and seals,
external fixing lugs

Sd 7 – empty, grey,
for VDE approved single terminals

332 907 01 60

Sd 7 – 2,5², grey,
5 interlockable screw terminals 2,5 mm²

332 407 01 60

Sd 7 – SL, grey,
5 screwless terminals 5 x 1,0-2,5 mm²

332 807 01 60