
Item no.: 733-106
Product description: FEMALE PLUG; WITH CODIG FINGERS; 6 POLE; PIN SPACING 2.5 MM / 0.098 IN; 100% PROTECTED AGAINST MISMATING; CAGE CLAMP®CONNECTION



Packing unit 100 pieces

Pin spacing from	2,5 mm
Pin spacing from	0,098 in
pole count	6
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	0,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	20 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	250 V
Measured shock voltage	2,5 kV
Pollution degree	2
Current intensity EN	4 A
Voltage CSA	150 V
Current CSA	4 A
Voltage UL	150 V
Voltage UL	250 V
Current UL	4 A
Weight	2,66 g
Color	light grey
No. of connection Points	6
No. of potentials	6
Height	11,8 mm



Width	17,5 mm
Width	0,689 in
Depth	17,1 mm
Depth	0,673 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0,22 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
733-106	ABS	04-HG469925-PDA	250	4	0,8-0,5
733-106	BV	11915/A0	250	4	0,8-0,5
733-106	CCA	NL5640	250	4	0,8-0,5
733-106	CSA	154112-1465035	150	4	28-20
733-106	CSM	017956	250	4	0,8-0,5
733-106	DEMKO	00-00102	250	4	0,5
733-106	DNV	E-6997	250	4	0,8-0,5
733-106	GL	17296-00HH	250	4	0,8-0,5
733-106	KEMA	2077592.01	250	4	0,8-0,5
733-106	LR	96/20035	250	6	0,8-0,5
733-106	RMR	11130002	250	4	0,8-0,5
733-106	RosTesT	B09523	250	4	0,8-0,5
733-106	UL	E45171	250	4	28-20
733-106	UL	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected