

**SONY**  
make.believe.

## DAV-DZ280

► <http://www.sony.co.uk>

This document was created on  
02-Oct-2009

5.1 channel DVD home cinema system. 850W total output power, HDMI™ upscaling to 1080p, USB playback and recording, an ultra-compact subwoofer and an iPod®/iPhone™ dock



## Features

Please be aware that the features/specifications can differ from country to country.

- Get stunning Sony sound quality from your iPod® or iPhone™ with the included iPod®/iPhone™ dock
- Pumps out a total of 850 W room filling sound from a central speaker, 4 satellite units and a 160mm ultra-compact subwoofer
- Hear your movies come to life with Dolby® Digital, Dolby® Prologic II and DTS Decoding
- S-Master digital amplifier delivers crystal clear sound for playback faithful to the original source
- Built-in upscaler generates a 1080p signal via HDMI™ cable for superb picture quality on your High Definition TV
- BRAVIA Sync for simple, integrated control with your BRAVIA TV and other compatible products using only one remote
- DCAC - one-push automatic sound set-up for flexible speaker placement and optimum sound quality
- DIGITAL MEDIA PORT - connect to and release digital music stored on your WALKMAN®, iPod® or other mp3 players, mobile phones, Bluetooth® and Wi-Fi devices
- Portable Audio Enhancer function improves the sound quality of compressed music such as mp3
- Rip CDs directly to your USB device, WALKMAN® or WALKMAN® phone
- Dialogue Enhancer keeps speech clear while limiting the volume of sudden sound effects - ideal for late night viewing
- FM radio tuner with RDS and 30 station presets

### Useful Links

- Product support
- <http://www.sony.co.uk>

- Movie / music modes optimise your audio settings automatically
- Multiple format and codec support - DVD / CD / Video CD / SACD / mp3 / JPEG playback capability

---

## Technical specifications

---

### Amplifier

Power Output - Center (RMS)	142 W
Power Output - Front (RMS)	142 W x2
Power Output - Subwoofer (RMS)	140 W
Power Output - Surround (RMS)	142 W x2
Power Output - Total (RMS 10%)	850 W
S-Master	YES

### DVD / SACD / VCD / CD Player & Recorder

CD-R / CD-RW Play Back	YES / YES
D / A Converter (Video)	108 MHz / 12 bit
DivX®	NO
DVD / CD / SACD TEXT	YES / YES / YES
DVD / DVD Audio / SACD / CD / Video CD	YES / - / YES / YES / YES
DVD-R / +R / +R DL / +RW / -RW / -RW (VR) Playback (* Some discs may not be played back)	YES / YES / YES / YES / YES / YES
DVD-RW (CPRM) Playback	NO
JPEG Playback	YES
mp3 Playback	YES
mp3 / ID3Tag Ver.1.1 / ID3Tag Ver.2.0	YES / YES / YES
Mechanism Tray Lock	YES
Mechanism Type	1 disc tray
OSD control	YES
Picture Navigator	YES
Play Mode (Shuffle / Program / Repeat) CD / VCD / SACD only	YES / NO / YES
Shuffle: DVD / CD / VCD / SACD	- / YES / YES / YES
Program: DVD / CD / VCD / SACD	- / YES / YES / -
Repeat: DVD / CD / VCD / SACD	YES / YES / YES / YES
Precision Cinema Progressive	YES
Progressive Scan (NTSC / PAL)	YES / YES
VCD Version 2.0	YES

### Equalizer

Portable Audio Enhancer	YES
Night Mode	YES
Dynamic bass boost	YES

---

#### Function

DVD	YES
TUNER (FM, AM)	FM
DIGITAL MEDIA PORT	YES
SAT	NO
TV	YES
USB	YES
AUDIO IN	YES

---

#### Input / Output

Audio Line IN (Analog)	NO
Audio Line IN (Optical)	NO
Audio Line IN (Coaxial)	NO
D.C.A.C. (Auto Calibration)	YES
SCART (TV audio in)	NO
SCART (COMPOSITE-out / RGB-out / AUDIO-in)	YES
Speaker Terminal (Front / Center / Surround / Subwoofer)	YES / YES / YES / YES
Video Signal OUT (Component)	NO
Video Signal OUT (HDMI™) Upscale720p / 1080i for DVD	YES (1080p)
DIGITAL MEDIA PORT	YES
Audio input (front, mini)	YES
iPod® / iPhone™ dock	YES (TDM-iP20)

---

#### Others

DEMO Mode	YES
Dimmer	YES
Timer (REC / PLAY / SLEEP)	YES (- / - / YES)
VACS	YES
BRAVIA Sync	YES

---

#### Power adjustment

Power Consumption	150 W
Power Consumption at stand by	Less than 0.3 W
Power Save Mode	YES
Power Requirement	220V-240V AC , 50 / 60 Hz

---

#### Surround / Effects

A / V SYNC (Lip Sync)	YES
DTS	YES
Dolby® Digital	YES
Dolby® Prologic / Prologic I / Prologic II	- / - / YES
Movie / Music Mode	YES

---

### Tuner

Band	FM
External FM / AM Antenna	YES (75ohm) / -
RDS ( PS / PTY / EON)	YES / - / -
Station Preset	FM20
Tuning Range (FM)	87.50 ~ 108.00 MHz (50kHz step)

---

[Terms of Use](#) | [Privacy statement](#)