

GP Batteries


Product Specification

Model No.: GPPB11BS

Description	:	Continuous NiMH Battery Charger with Night Light Function (Plug-In Type)
Input Voltage	:	230V AC 50Hz
Input Power	:	10 W
Application	:	For charging 2 or 4 pcs NiMH AA and/or AAA batteries; and 1 or 2 pcs NiMH 9V batteries
Output Voltage	:	2.8V DC (AA/AAA); 9V DC (9V)
Charging Current	:	AA 130mA +/- 15% AAA 70mA +/- 15% 9V 17mA +/- 15%

Charging Time	:	<table border="1"> <thead> <tr> <th>Size</th> <th>Capacity</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td rowspan="3">AA</td> <td>1900mAh</td> <td>~ 21 hrs</td> </tr> <tr> <td>1800mAh</td> <td>~ 20 hrs</td> </tr> <tr> <td>1600mAh</td> <td>~ 16 hrs</td> </tr> <tr> <td rowspan="3">AAA</td> <td>1300mAh</td> <td>~ 14 hrs</td> </tr> <tr> <td>800mAh</td> <td>~ 16 hrs</td> </tr> <tr> <td>750mAh</td> <td>~ 15 hrs</td> </tr> <tr> <td rowspan="2">9V</td> <td>700mAh</td> <td>~ 14 hrs</td> </tr> <tr> <td>170mAh</td> <td>~ 14-16 hrs</td> </tr> </tbody> </table>	Size	Capacity	Time	AA	1900mAh	~ 21 hrs	1800mAh	~ 20 hrs	1600mAh	~ 16 hrs	AAA	1300mAh	~ 14 hrs	800mAh	~ 16 hrs	750mAh	~ 15 hrs	9V	700mAh	~ 14 hrs	170mAh	~ 14-16 hrs
Size	Capacity	Time																						
AA	1900mAh	~ 21 hrs																						
	1800mAh	~ 20 hrs																						
	1600mAh	~ 16 hrs																						
AAA	1300mAh	~ 14 hrs																						
	800mAh	~ 16 hrs																						
	750mAh	~ 15 hrs																						
9V	700mAh	~ 14 hrs																						
	170mAh	~ 14-16 hrs																						


MTBF	:	30000 hours (at ambient temperature 25°C)
Operating Temperature	:	0°C to 45°C
Storage Temperature	:	-25°C to 60°C
Charge Indicator	:	LED for each channel; two channels operate individually.
Dimensions	:	130(L) X 75(W) X 40.5(T)mm
Approval	:	CE
Warranty Period	:	12 months from ex-factory date.



*Front view

Unit : mm

NOTE : It is safe to charge GP NiMH batteries continuously with GP PowerBank Nite-lite .



Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

010301713