


QLK45/1818-3030

AC tangential blower

forward curved



ebm-papst Landshut GmbH

Hofmark-Aich-Straße 25

84030 Landshut

Phone: +49 871 707-0

Fax: +49 871 707-465

www.ebmpapst.com

info3@de.ebmpapst.com

Nominal data


Type	QLK45/1818-3030	
Nominal voltage	[VAC]	230
Frequency	[Hz]	50
Speed	[min ⁻¹]	2200
Power input	[W]	32
Current draw	[A]	,265
Max. back pressure	[Pa]	59
Min. ambient temperature	[°C]	0
Max. ambient temperature	[°C]	60
Air flow	[m ³ /h]	220

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations


Technical features

Dimensions	45 mm
General description	With double housing
Connection line	Flat plug 6.3 x 0.8
Line	Compact series
Mounting position	Horizontal
Insulation class	B F or H also available on request
Mass	2.15 kg

Product drawing



Charts: Air flow



Charts: Speed

