



SPECIFICATIONS

- Wire: Reinforced insulation silicone (-60°C ~ 180°C)
196X0.07mm Stranded Bare Copper, (0.75mm²) Cross Section,
0.142±.008 [3.6±0.2mm] O.D.
- Insulated Housing: PA6 (Nylon) Thermoplastic, UL94V-0
- Contact: 4mm, 9 Leaf-BeCU, Nickel Plated,
- Plug Body and Jack: Brass, Nickel Plated

Rating:

- Voltage: 1200V AC/DC
- Current: 12A Max.
- Resistance: 20 milliohms Max., 100cm Length
- Temperature: -20°C ~ 80°C

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION
AND/OR TESTS WE BELIEVE TO BE