



Sample photo

Order symbol: CAB PC 302018 T
Product nbr: 8113030
Description: Cabinet, PC
Remarks: Latches on the long side, smooth

EAN: 6418074020017
EI. number:
 Finland 3424151
 Denmark 8212020210
 Italy 7822015
 Sweden 2539935

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		L	W	H	Rating:
mm:		300	200	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	7.9	7.1	Impact Resistance (EN 50102): IK 08
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Gasket material:		EPDM			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKIV 23		Mounting plate			
EKIV 17		DIN-35 Mounting rail			
EKIV 27		DIN-35 Mounting rail			
FP A 23		Swing-out door, aluminium			
FP 23		Front plate			
FP 12-23		Front Plate			
DRF 23		DIN rail frame set			
DRF 33		DIN rail frame set			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Fimko			
		Lloyds Register of Shipping (LR)			
		Europe EN 50298 1998			
		UL Canada			
		Gost R			
		Electrical insulation: Totally insulated			
		Halogen free (DIN/VDE 0472, Part 815): Yes			
		UV resistance: UL 508			
		Flammability Rating (UL 746 C 5): UL 94 5V			
		Glow Wire Test (IEC 695-2-1) °C: 960			
		UL Type: UL TYPE 1, 4, 4X, 12, 13			

