




Sample photo

Order symbol: CAB ABS 403018 G
Product nbr: 8183350
Description: Cabinet, ABS
Remarks: Latches on the long side, smooth

EAN: 6418074020260
El. number:
 Finland 3424314
 Denmark 8212020540
 Italy 7811040
 Sweden 2540071

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			L		W		H	
mm:	400	300	180					
inch:	15.7	11.8	7.1					
Materials:								
Material:	ABS							
Base colour:	RAL 7035							
Cover colour:	RAL 7035							
Gasket material:	EPDM							
Temperatures:								
Short term:	-40 ... 80 °C							
Continuous:	-40 ... 60 °C							
Short term:	-40 ... 175 °F							
Continuous:	-40 ... 140 °F							
Accessories:								
EKIV 43	Mounting plate							
EKIV 27	DIN-35 Mounting rail							
EKIV 37	DIN-35 Mounting rail							
FP A 43	Swing-out door, aluminium							
FP 43	Front plate							
FP 12x2-43	Front Plate							
FP 12x3-43	Front Plate							
DRF 43/44	DIN rail frame set							
Rating:								
Ingress Protection (EN 60529): IP 65								
Impact Resistance (EN 50102): IK 08								
Electrical insulation: Totally insulated								
Halogen free (DIN/VDE 0472, Part 815): Yes								
Flammability Rating (UL 746 C 5): UL 94 HB								
Glow Wire Test (IEC 695-2-1) °C: 650								
NEMA Class: NEMA 1, 4, 4X, 12, 13								
Certificates:								
Fimko								
Europe EN 50298 1998								
Gost R								



(c) Fibox OY, Data subject to change without notice