



IR-77

Pocket Infrared Thermometers

The IR-77, Pocket Infrared Thermometers are new models design with lower cost. Check all types of A/C and heating systems. Monitor performance of appliances such as refrigerator, dishwasher, freezer and oven. Ensure proper cooking, grilling and storage temperatures.

- 6:1 Distance to Spot size ratio (measures a 6 inch area one foot away)
- Easy to use: hold it within two feet of the area to be measured and push the button
- Large LCD screen shows readings in Fahrenheit or Celsius
- Range: -30 to 270°C / -22 to 518°F

Features

User selectable °C or °F
Automatic Data Hold
Auto Power Off
Backlit LCD Display
Low battery indication

Specifications

Range	-30°C~270°C/-22°F~518°F
Response Time	less than one second
Resolution	1°C/°F
Basic Accuracy	±2% or ±2°C/±4°F
Optical Resolution	6:1
Emissivity	Fixed at 0.95
Battery	1.5V AAA battery x 2

Size(HxWxD): 97mm x 57mm x 29mm

Weight: 81g

Accessories: Two "AAA" Batteries and Manual, Packing: Clamshell