

DC axial fan

Series 500 F 50 x 50 x 15 mm



- **General description:** DC fan with electronically commutated external rotor motor. Commutation electronics completely integrated.

- **Impeller material:** Fiberglass-reinforced PA plastic

- **Housing material:** Fiberglass-reinforced PBT plastic

Nominal data

Type	Motor	Voltage VDC	Voltage range VDC	Air flow m ³ /h	Speed 1/min	Power consumption W	Sound level Bel	Sound pressure level dB(A)	Ambient temperature °C	L10 service life at max. temp. h	Weight kg
514 F	--	24	21.6 - 26.4	20	5000	1.0	4.5	30	-20 .. 70	20000	0.025

Subject to modification

Characteristic: Pressure over air flow



