

## PBPA / PBPS PANELS

for more information visit


[www.hammondmfg.com](http://www.hammondmfg.com)

Data subject to change without notice

### PART No. PBPA & PBPS19001BK2


PBPA MATERIAL: 0.125" THK ALUMINUM

PBPS MATERIAL: 14 GA. STEEL








## Aluminum Rack Panels (PBPA Series)

















Path: [Home](#) > [Rack Index](#) > Aluminum Rack Panels (PBPA)



















### Features:


- 0.125" thick, easy to machine aluminum...
- Standard 19" rack panels...
- Painted versions are finished in powder paint...
- Smooth paint finish for easy labelling...
- Unfinished version is white paper covered on one side to protect finish - also used as a surface for a machining template (see photo below)...
- Standard rack mount punching on both ends...
- Requires mounting [hardware](#)

Part Number	Color	Reader File	 Drawing File Size	AutoCAD .dxf File	.dxf File Size	Panel Height		No. of Slots
						Inches	Units	
<a href="#">PBPA19001BK2</a> <a href="#">PBPA19001CG2</a> <a href="#">PBPA19001GY2</a> <a href="#">PBPA19001UNF</a>	Black Gray/Beige ASA 61 Gray Unfinished		13K		74K	<b>1.75</b>	1	4
<a href="#">PBPA19003BK2</a> <a href="#">PBPA19003CG2</a> <a href="#">PBPA19003GY2</a> <a href="#">PBPA19003UNF</a>	Black Gray/Beige ASA 61 Gray Unfinished		13K		74K	<b>3.50</b>	2	4

<b>PBPA19005BK2</b>	Black		13K		74K	<b>5.25</b>	3	4
<b>PBPA19005CG2</b>	Gray/Beige							
<b>PBPA19005GY2</b>	ASA 61 Gray							
<b>PBPA19005UNF</b>	Unfinished							
<b>PBPA19007BK2</b>	Black		13K		74K	<b>7.00</b>	4	4
<b>PBPA19007CG2</b>	Gray/Beige							
<b>PBPA19007GY2</b>	ASA 61 Gray							
<b>PBPA19007UNF</b>	Unfinished							
<b>PBPA19008BK2</b>	Black		13K		74K	<b>8.75</b>	5	4
<b>PBPA19008CG2</b>	Gray/Beige							
<b>PBPA19008GY2</b>	ASA 61 Gray							
<b>PBPA19008UNF</b>	Unfinished							
<b>PBPA19010BK2</b>	Black		13K		88K	<b>10.50</b>	6	8
<b>PBPA19010CG2</b>	Gray/Beige							
<b>PBPA19010GY2</b>	ASA 61 Gray							
<b>PBPA19010UNF</b>	Unfinished							
<b>PBPA19012BK2</b>	Black		13K		88K	<b>12.25</b>	7	8
<b>PBPA19012CG2</b>	Gray/Beige							
<b>PBPA19012GY2</b>	ASA 61 Gray							
<b>PBPA19012UNF</b>	Unfinished							
<b>PBPA19014BK2</b>	Black		13K		88K	<b>14.00</b>	8	8
<b>PBPA19014CG2</b>	Gray/Beige							
<b>PBPA19014GY2</b>	ASA 61 Gray							
<b>PBPA19014UNF</b>	Unfinished							
<b>PBPA19015BK2</b>	Black		13K		88K	<b>15.75</b>	9	8
<b>PBPA19015CG2</b>	Gray/Beige							
<b>PBPA19015GY2</b>	ASA 61 Gray							
<b>PBPA19015UNF</b>	Unfinished							
<b>PBPA19017BK2</b>	Black		13K		88K	<b>17.50</b>	10	8
<b>PBPA19017CG2</b>	Gray/Beige							
<b>PBPA19017GY2</b>	ASA 61 Gray							
<b>PBPA19017UNF</b>	Unfinished							

<b>PBPA19019BK2</b>	Black		13K		88K	<b>19.25</b>	11	8
<b>PBPA19019CG2</b>	Gray/Beige							
<b>PBPA19019GY2</b>	ASA 61 Gray							
<b>PBPA19019UNF</b>	Unfinished							
<b>PBPA19021BK2</b>	Black		13K		88K	<b>21.00</b>	12	8
<b>PBPA19021CG2</b>	Gray/Beige							
<b>PBPA19021GY2</b>	ASA 61 Gray							
<b>PBPA19021UNF</b>	Unfinished							
<b>PBPA19022BK2</b>	Black		13K		88K	<b>22.75</b>	13	8
<b>PBPA19022CG2</b>	Gray/Beige							
<b>PBPA19022GY2</b>	ASA 61 Gray							
<b>PBPA19022UNF</b>	Unfinished							
<b>PBPA19024BK2</b>	Black		14K		95K	<b>24.50</b>	14	10
<b>PBPA19024CG2</b>	Gray/Beige							
<b>PBPA19024GY2</b>	ASA 61 Gray							
<b>PBPA19024UNF</b>	Unfinished							
<b>PBPA19026BK2</b>	Black		14K		95K	<b>26.25</b>	15	10
<b>PBPA19026CG2</b>	Gray/Beige							
<b>PBPA19026GY2</b>	ASA 61 Gray							
<b>PBPA19026UNF</b>	Unfinished							
<b>PBPA19028BK2</b>	Black		14K		102K	<b>28.00</b>	16	12
<b>PBPA19028CG2</b>	Gray/Beige							
<b>PBPA19028GY2</b>	ASA 61 Gray							
<b>PBPA19028UNF</b>	Unfinished							
<b>PBPA19029BK2</b>	Black		14K		102K	<b>29.75</b>	17	12
<b>PBPA19029CG2</b>	Gray/Beige							
<b>PBPA19029GY2</b>	ASA 61 Gray							
<b>PBPA19029UNF</b>	Unfinished							
<b>PBPA19031BK2</b>	Black		14K		102K	<b>31.50</b>	18	12
<b>PBPA19031CG2</b>	Gray/Beige							
<b>PBPA19031GY2</b>	ASA 61 Gray							
<b>PBPA19031UNF</b>	Unfinished							

**Unfinished Feature:**



(click to enlarge)

Unfinished version is white paper covered on one side to protect finish - also used as a surface for a machining template

---

DOWNLOAD



[Rack panel catalog pages \(2\)](#) - Adobe Reader .pdf format (105K)

DOWNLOAD



[all accessories - catalog pages \(44\)](#) - Adobe Reader .pdf format (1,495K)

---

## ***Mail Link To Our Catalog Department***

**[Provide full mailing address here for your FREE CATALOG via snail mail...](#)**

---

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check