


C1812C224J5GAC

aka C1812C224J5GAC

Capacitor, ceramic, 0.22 uF, +/-5% Tol, 50V, C0G, 1812



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	4.5	+/-0.3	Capacitance:	0.22 uF
W	3.2	+/-0.3	Chip Size:	1812
T	1.6	+/-0.2	Voltage:	50V
B	0.6	+/-0.35	Temperature Coefficient:	C0G
			Tolerance:	+/-5%
			Application:	Standard Chip
			Termination Type:	Tin
			Marking:	Unmarked
			Dissipation Factor:	0.1%
			Insulation Resistance:	4.54545 GOhm
			Dielectric Strength:	125V
			Package Quantity:	1
			Packaging:	Bulk, Bag