



- Identification ties with incorporated label for durable marking and tying
- Label forms onto the bundle for types TY512M, TY51M and protrudes for ties TY532M and TY53M
- Type 51M is MIL (MS-3368-5) approved
- Trouble-free installation
- Simple marking on the roughened writing surface using the special marking pen WT163M-1 (black ink) or WT163M-3 (red ink) - See page 29
- All edges are rounded to make installation easier



TY532M & TY53M



TY512M & TY51M



Technical Information

Material - Moulding	Polyamide 6.6
Material - Locking barb	316 grade stainless steel
Temperature range	-40°C to +85°C
Colour	Natural
Flammability rating	UL 94 V-2
Other properties	Halogen free, Silicone free

Approvals



E49405

Ordering Information

PRODUCT REF.	MIL SPEC.	LENGTH	WIDTH	THICKNESS	BUNDLE DIAMETER	MINIMUM TENSILE	LABEL	QUANTITY	TOOLING
		L [mm]	W [mm]						
TY51M	MS-3368-5	92	2.4	1.0	10 - 16	80	25.4 x 7.9	500	
TY512M	-	210	2.4	1.0	10 - 51	80	25.4 x 7.9	1000	WT193A
TY53M	-	102	2.4	1.0	2 - 16	80	20.6 x 9.3	500	ERG299
TY532M	-	212	2.4	1.0	2 - 51	80	20.6 x 9.3	1000	TR227

For other materials and colours contact your Sales Office
For tooling specifications see pages 92 to 99