

RATCHET WRENCHES

"11-in-1" ratchet wrench set Ideal for on-site maintenance!

464
PRODUCTIVITY



RATCHET WRENCHES 464.J1PB

- Place the desired ring size in the wrench in one click
- Secure one-handed locking system

- The rings are securely held in their foam compartments even if the case is dropped or overturned.
- Foam tray and box resistant to impact and workshop chemicals



ULTRA-LIGHTWEIGHT

- 60% lighter than, a set of six ring wrenches.

COMPACT

- Low profile head: 3 times narrower than the ratchet and socket system



Used as a pass-through wrench on long threads



- No time wasted searching for the required size.
- Very visible marking.



464.J1PB
3148518240772

"11-in-1" ratchet wrench set

- 5° increments
 - FACOM performance: torsional strength = ISO 1711-1 + 50%
 - Comprehensive selection: 8-9-10-11-12-13-14-15-16-17-19 mm
- ΔΔ : 0,517 kg.

New ratchet combination wrenches Ultra-compact, ultra-accessible, multi-application!

467^S
PRODUCTIVITY

The adaptors transform the wrench into an ultra-compact ratchet for sockets and bits.



ULTRA-COMPACT

The adaptors transform the wrench into an ultra-compact ratchet for sockets and/or bits.

Head of height + socket:
27% more compact than the ratchet + socket.

REACH ANYWHERE

- Foam tray:
 - Visual identification of missing tools,
 - Holds tools securely even upside-down.



MULTI-APPLICATION

- "Standard" configuration
- "Socket" configuration
- "Bit" configuration

4675.B0XPB
3148518240857



Ultra-compact multi-application set

- 4675 7 8 9 10 11 12 13 14 mm
 - 1/4" R. 5,5 -6-7-8-9-10-11-12-13-14 mm
 - 1/4" + 1-2-3 - 4,5-6,5-8 1-2-3 10-15-20-25-30-40 3-4-5-6-7
 - 1/4" 55 mm Extension
 - Wrench adaptor 10mm 1/4" : 467.ADAPT10MM
- ΔΔ : 0,884 kg.

