


CTFP Series - PCB Mounting Transformers

- Dual Primary 115V windings
- Dual secondary windings
- Power: 3 to 12VA, 50/60Hz
- Temperature class: B (130°C)
- Dielectric strength: 3750V_{rms}
- ULV0 rated material
- Manufactured and tested in accordance with EN60950 and EN61558



CTFP Series



VA	Part No	Output VAC x2
3	CTFP3-6	6
3	CTFP3-9	9
3	CTFP3-12	12
3	CTFP3-15	15
3	CTFP3-20	20
6	CTFP6-6	6
6	CTFP6-9	9
6	CTFP6-12	12
6	CTFP6-15	15
6	CTFP6-20	20
12	CTFP12-9	9
12	CTFP12-12	12
12	CTFP12-20	20

VA Rating	Dimension (mm)										PCB Hole	Weight (g)
	A	B	C	D	E	F	G	H	I			
3	38	32	30	4	25	5	Sq 0.7				1.2	140
6	43	36	32	4	25	5	1.0 x 0.7	45	36		1.2	180
12	54	45	39	4	30	5	1.0 x 0.7				1.2	340
Tolerance	±0.5	±0.5	±0.5	±1.0	±0.5	±0.2	±0.1					approx