

**IE-BS-V04P-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



A key feature of **STEADYTEC®** is the modular principle: plug and flange housings with a multitude of inserts. Here is an overview of the flanges for variant 4 in plastic.

Features:

- IP 67
- Cat.6A throughout for copper connections
- polyamide V-0
- standard pitch
- marker tag holder

**General ordering data**

Order No.	<a href="#">1963490000</a>
Part designation	IE-BS-V04P-RJ45-C
Version	Flange RJ45, IP 67, Version 4, coupling, Cat.6A / Class E <sub>A</sub> (IEC 11801 PDAM Am 1.2 2007)
EAN	4032248645589
Qty.	10 pc(s).

## IE-BS-V04P-RJ45-C

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

## Technical data

### temperature

Ambient temperature (operational) -40°C - +70°C

### Connection elements

Version	Socket	Connection 1	RJ45
Connection 2	RJ45	Protection class	IP 67
Housing main material	PA UL 94 V0	Category	Cat.6A / Class E <sub>A</sub> (IEC 11801 PDAM Am 1.2 2007)
Shielding	360° all-round enclosure	Plugging cycles	750 plugging cycles for plugs to IEC 60603-7

### Downloads

Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class E Category 6, 3 connector permanent link	ac107534.pdf	Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class E Category 6, 4 connector channel	ac107533.pdf
Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class EA Category 6A, 2 connector channel	ac107535.pdf	Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class EA Category 6A, 4 connector channel	z1755b-07-D.pdf
GOST Approval	POCC DE.ME25.B01411.pdf	UL Approval	E316369VOL1SEC4.pdf

### Approvals

Approvals institutes CULUS

### Classifications

eClass 5.1 27-26-12-03 eClass 6.0 27-26-12-03