

05.17.244

Hex-Standoff / Male - Female

Length	5,0 mm
Material	Steel QQ-S-637,ASTM-A-108
Plating	Zinc (yellow chromate) A3G
Thread I-1/Inside / Length	UNC4-40 / 3,4 mm
Thread A-2/Outside / Length	M2,5 / 8,0 mm
Hex Sizes or Dia.	5
Undercut	no
Model	Hex male / female nicht RoHS konform

