

05.17.374

Hex-Standoff / Male - Female

| | |
|-----------------------------|---|
| Length | 7,0 mm |
| Material | Steel QQ-S-637,ASTM-A-108 |
| Plating | Zinc (yellow chromate) A3G |
| Thread I-1/Inside / Length | UNC4-40 / 4,5 mm |
| Thread A-2/Outside / Length | M3 / 5,5 mm |
| Hex Sizes or Dia. | 5 |
| Undercut | yes |
| Model | Hex male / female nicht RoHS konform |

