

05.17.449

## Hex-Standoff / Male - Female

Length	4,9 mm
Material	Stainless Steel
Thread I-1/Inside / Length	UNC4-40 / 3,4 mm
Thread A-2/Outside / Length	UNC4-40 / 7,9 mm
Hex Sizes or Dia.	4,75
Undercut	no
Model	Hex male / female RoHS konform

