



L1790A BARRIER STRIP

These rugged 12 way terminal blocks are moulded in polyester, and are not subject to accidental chipping.
The L1790A has one row of screw terminals and one row of right angle through-chassis terminals for solder and solderless snap-on connections.

CURRENT RATING:	15A (using screw or soldered connections at 70°C maximum ambient) 5A (with fast on connections)
TEMPERATURE RANGE:	-55°C to +100°C (ambient)
VOLTAGE PROOF:	4 KV rms
CONTACT RESISTANCE:	≤3 milliohms
INSULATION RESISTANCE:	≥100 megohms
CREEPAGE RESISTANCE:	6.9mm (terminals to panel face)
TERMINATIONS:	2.8mm x 0.61mm for solderless snap on connections or solder.
MAXIMUM TORQUE (terminal screws):	0.7Nm
MATERIALS:	Moulding: polyester, black Terminals: brass, tinned Screws: steel, nickel plated 4 BA panhead
APPROVALS	None

ORDERING REFERENCE: L1790A



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>