




– In addition to the accessories and assembly parts listed in this catalogue, ebm-papst also supplies numerous special parts for fan operation. The sales experts at ebm-papst will be happy to assist you in your enquiries concerning fan assembly and application.

**ebm-papst St. Georgen**

### LZ120




Type	Cable length	Pins
LZ120	610 mm	0.5 mm
LZ126	1000 mm	0.5 mm
LZ130-1	610 mm, UL approved	0.5 mm

Additional versions are available on special order


Connecting cable with moulded plug, (PVC, black). Stranded wires with multi-core cable ends. For all types of fan with flat pins 3.0 x 0.5 mm.

### LZ212



Screw clip of rust-resistant spring steel. For mounting fans with threaded pin 3.5 DIN 7970.

### LZ260/LZ261




Spacer of fibreglass reinforced plastic. For screw mounting over both fan mounting flanges.

### LZ210



Screw clip of hardened steel. For mounting fans with threaded pin 6-32 UNC and/or 3.5 DIN 7970.

### LZ370



Required performance date:

$R_{25}$  = 100 K $\Omega$   $\pm$ 5%

B-value = 4190  $\pm$  2%

$P_{max}$  = 0,25 W

Temperature sensor for speed-controlled fan operation. Temperature range 30...50 °C.