

05.28.315

Hinged-Standoffs

| | |
|--------------------------------|-------------------------------------|
| Length | 15,0 mm |
| Material | Brass |
| Plating | Nickel plated |
| Thread I-1/Innside / Length | M3 / 6,0 mm |
| Thread A-2/Outside / Length | M3 / 9,0 mm |
| Type | Hinged Standoffs |
| Model | Inside/Outside |
| Thread 1 Lenght | 6,0 mm |
| Thread 2 Lenght | 9,0 mm |
| Model | Schenkel ungleich |
| Special | □0043363163Gew.Teil RoHS konform |

