

05.53.033 **Round Spacer-Brass /
Wall Thickness 1,4 mm**

Length	3,0 mm
Material	Brass QQ-B-6261 ASTM-B-16
Plating	Nickel plated
Inside Diameter	for M3= Dia. 3.0-3.5
Outside Diameter	6,0 mm
Model	Round Spacer
Type	Standard, Endsite Plain
Attribute	gedreht
Design	Cuttet
Special	□004T 6,0mm rd RoHS konform

