


# Section 13

## Retail Products



## Cordline switch



Pack	Cat No.	Cordline switch
10	D5M	Cordline switch for wiring onto either 3-core or figure-8 two-wire cable. Double pole, 10A. Available in white or black

5	D817/2	7 day digital timer. Digital accuracy and advanced functions. Battery backup. Up to 14 on/off switches each day
6	D817DUSK	Dusk-Dawn timer turns on at Dusk. Set to stay on for 1 - 8 hours or until sun comes up. Also has random and countdown functions.
6	D817SMART	Smart Security switch. Records daily patterns and replays them for a realistic routine. Easy to use.

## Timers



Pack	Cat No.	10A Plug-in timers
6	D809/1	24 hour timer. Up to 48 on/off switches each day. Offset design keeps adjacent outlet free
6	D809/1TWIN	Twin pack 24 hour timers. Up to 48 on/off switches each day. Offset design keeps adjacent outlet free
6	D811/7DAY	7 day timer. Offset design keeps adjacent outlet free. Up to 48 on/off switches per week
6	D809/1HP	Twin pack 1 x 24 hour and 1 x 7 day timer. Offset design keeps adjacent outlet free
5	D810/2	24 hour compact timer. Up to 48 on/off switches each day. Perfect for small spaces
6	D810SLIM	Slimline 24 hour timer. Fit 2 timers side by side in a powerpoint
6	D810SLIMTP	Twinpack slimline 24 hour timer
4	D818	10A 24 hour heavy duty timer. M40 motor rating for heavy duty appliances. Easy set push-tab operation
5	D819	10A 24 hour lamp and appliance timer. Just 2 rotating arrows to set. Override switch
6	D819/2	10A 24 hour easy set security timer with 2 ON-OFF/s power day. 4 rotating arrows to set, override switch
6	D812COUNT4	4 hour countdown timer. Switches appliances off within 4 hours
5	D812HOL	Holiday set'n'go timer. Pre-set 'random' function for easy use and weekly unpredictable switching pattern

## Door chimes



Pack	Cat No.	All D641 series wireless door chimes & bell presses are compatible. Choice of two chime tones - Ding Dong or Westminster. <b>Battery operated door chimes</b> Bell press battery included.
8	D641/B	Battery door chime with bell press, up to 30m range. Can be used as pager or panic switch.
5	D641/BLR	Long range door chime with bell press, up to 70m range. Name insert on bell press. Available in white or charcoal.
5	D641/BFL	Deluxe door chime with flashing light and weatherproof bell press, up to 70m range. 3 volume settings. 3 year warranty.



Pack	Cat No.	Plug in door chimes Bell press battery included.
5	D641/PI	Plug-in door chime with weatherproof bell press, up to 30m range. Suits any standard outlet.
5	D641/PILR	Long range door chime with weatherproof bell press, up to 70m range. Includes piggy-back socket.
5	D641/PIFL	Deluxe door chime with flashing light and weatherproof bell press, up to 70m range. Includes piggy back socket. 3 volume settings. 3 year warranty.



Pack	Cat No.	Bell press
10	D641/BP	Additional weatherproof bell press for D641 series door chimes. Available in white or charcoal. 3 year warranty.
8	D651	Wireless door phone. Up to 80m range, DIY installation.



Pack	Cat No.	Household duty extension leads, 10A, 240V a.c.
10	R2702	2m white household duty extension lead.
10	R2703	3m white household duty extension lead.
5	R2705	5m white household duty extension lead.
5	R2707	7m white household duty extension lead.
5	R2710	10m white household duty extension lead.
5	R2715	15m white household duty extension lead.
4	R2720	20m white household duty extension lead.

## Movement sensors (PIR's)



Pack	Cat No.	Movement sensors
3	D630/3A	Light Patrol security sensor with 180° field of view, auto only

## Smoke alarms

Pack	Cat No.	Smoke alarm
4	D645/2	Smoke alarm with low battery warning. 9V battery included. SSL approved



Pack	Cat No.	Heavy duty extension leads, without clamping socket, 10A, 240V a.c.
5	R2810	10m yellow heavy duty lead with clear socket and plug
5	R2815	15m yellow heavy duty lead with clear socket and plug
5	R2820	20m yellow heavy duty lead with clear socket and plug
5	R2825	25m yellow heavy duty lead with clear socket and plug

## Extension leads



Pack	Cat No.	All lead lengths are nominal lengths. Household duty piggy-back extension leads, 10A 240V a.c.
10	R2601	1m white household duty extension lead with piggy-back plug
10	R2602	2m white household duty extension lead with piggy-back plug
10	R2604	4m white household duty extension lead with piggy-back plug
5	R2606	6m white household duty extension lead with piggy-back plug
5	R2610	10m white household duty extension lead with piggy-back plug



Pack	Cat No.	Heavy duty extension leads, with clamping socket, 10A, 240V a.c.
5	R2810L	10m yellow heavy duty lead with clear clamping socket and clear plug
5	R2815L	15m yellow heavy duty lead with clear clamping socket and clear plug
5	R2820L	20m yellow heavy duty lead with clear clamping socket and clear plug
5	R2825L	25m yellow heavy duty lead with clear clamping socket and clear plug



Pack	Cat No.	<b>Garden heavy duty extension leads with clamping socket, 10A, 240V a.c.</b>
5	R2815GL	15m yellow & black heavy duty lead with clamping socket and parking clip
5	R2825GL	25m yellow & black heavy duty lead with clamping socket and parking clip



Pack	Cat No.	<b>Caravan and construction lead, 15A, 240V a.c.</b>
5	R2908/15	8m orange extra heavy duty caravan lead. Clear 15A plug & clear 15A socket
5	R2920/15	20m orange extra heavy duty lead. 15A clear socket & 15A clear plug.



Pack	Cat No.	<b>Plug Boss™ heavy duty extension leads with clamping socket, 10A, 240V a.c.</b>
5	R2810PBL	10m yellow & black heavy duty lead with clamping socket and parking clip
5	R2820PBL	20m yellow & black heavy duty lead with clamping socket and parking clip



Pack	Cat No.	<b>Safety cord lock</b>
5	D107	Locks 3 pin plugs & extension sockets safely together. Fits all standard size plugs & sockets. Yellow
32	RHH01	<b>Extension lead carry straps, for carrying leads and hoses up to 5kg</b> Hang and hold lead strap. Orange



Pack	Cat No.	<b>Tradesman extra heavy duty extension leads, 10A, 240V a.c.</b>
5	R2920	20m orange extra heavy duty lead. 10A clear socket & 10A clear plug. 15A lead
3	R2930	30m orange extra heavy duty lead. 10A clear socket & 10A clear plug. 15A lead
3	R2935	35m orange extra heavy duty lead. 10A clear socket & 10A clear plug. 15A lead

## Double adaptors



Pack	Cat No.	<b>Double adaptors</b> Available in white only
5	D2	Slimline twin adaptor, 10A. Projects to the right of the powerpoint
5	D2L	Slimline twin adaptor, 10A. Projects to the left of the powerpoint
5	D2/2	Pack of two twin adaptors, one left-projecting the other right-projecting, to turn a double outlet into a four-way outlet
10	D102	Conventional triangular double adaptor, 10A
20	R102	Conventional triangular double adaptor, 10A. Box of 20 (price quoted 'each')

## Surge protected adaptors



Pack	Cat No.	Surge protected twin adaptors, 240V a.c.
5	D2PA	Plug-in slimline twin adaptor offers protection against surges and spikes on the mains supply Neon indicates 'protection working'. Rated to 10 Amps.
5	D2PAB	Plug-in twin adaptor with audible buzzer warning when protection is no longer available. Rated to 10A



Pack	Cat No.	Surge protected outlet, 240V a.c.
5	D2PARJ	10A plug-in surge protector 1 surge protected power outlet plus surge protected phone/data/modem/internet line.

## Powerboards



Pack	Cat No.	All lead lengths are nominal lengths unless otherwise stated <b>Household Powerboards with overload protection, 240V a.c.</b>
8	D105/4TR	4 outlet powerboard with spacing for up to 2 plug-in transformers, 0.9m lead, 10A. White
5	D105/1	4 outlet powerboard, 1.8m lead, 10A. White
5	D105/5TR	5 outlet powerboard with spacing for up to 3 plug-in transformers, 1.8m lead, 10A. White
5	D105/6	6 outlet powerboard, 0.9m lead, 10A. White
5	D105/80LN	8 outlet powerboard, 1.8m lead, 10A. White
8	D105/12TR	12 outlet powerboard with spacing for 3 transformers and 1.8m lead, 10A, White

1	R105	Box of 10, 4 outlet powerboard, 0.9m lead, 10A. White. Must be ordered in box quantities
1	R105/6	Box of 10, 6 outlet powerboard, 0.9m lead, 10A. White. Must be ordered in box quantities
8	D105SS4	<b>Child-safe™ powerboards with overload protection, 240V a.c.</b> 4 outlet powerboard with rotating child safety covers, 0.9m lead, 10A, White
8	D105SS6	6 outlet powerboard with rotating child safety covers, 1.8m lead, 10A, White
8	D105SSPA4	4 outlet powerboard with rotating child safety covers and 150J surge protection, 0.9m lead, 10A, White
8	D105SSPA6	6 outlet powerboard with rotating child safety covers and 150J surge protection, 1.8m lead, 10A, White



Pack	Cat No.	Switched powerboards, 240V a.c. Individually switched outlets with overload protection.
5	D104	4 outlet powerboard, 0.9m lead, 10A. White
5	D104/1	4 outlet powerboard, 1.8m lead, 10A with customised switch inserts, safety plugs and switch lock. White
5	D104PA	4 outlet powerboard, 1.8m lead, 10A with customised switch inserts, safety plugs and switch lock with surge protection. White
5	D104/6/1	6 outlet powerboard, 1.8m lead, 10A with customised switch inserts, safety plugs and switch lock. White



Pack	Cat No.	Entertainment powerboards with surge protection and overload protection 240V a.c.
8	D105/4TRPA	4 outlet powerboard with spacing for 2 transformers and 150J surge protection, 0.9m lead, White
5	D105/5TRPA	5 outlet powerboard with spacing for 3 transformers and 150J surge protection, 1.8m lead, 10A, White
5	D105PA6	6 outlet powerboard with 150J surge protection, 0.9m lead, 10, White

5	D105PA6CC	6 outlet powerboard with 150J surge protection, 1.8m lead, 10, Charcoal
5	D105PP4	1 Entertainment powerboard with 4 outlets, 450J surge protection, and RFI filtering on poweroutlets, 1.8m lead, 10A, White
5	D105PP6	Entertainment powerboard with 6 outlets, 450J surge protection, and RFI filtering on poweroutlets, 1.8m lead, 10A, White

4	D105PB0SSPA6	6 outlet powerboard with 350J surge protection, spacing for up to 2 transformer plugs, illuminated on/off switch, cable management, "parking clip" plug, 3.1m lead, 10A, yellow
4	D105PB0SSELPA8	8 outlet powerboard with Electresafe RCD safety switch, 350J surge protection & rotating dust covers, illuminated on/off switch, cable management, "parking clip" plug, spacing for up to 2 transformer plugs, 3.1m lead, 10A

## Surge protected powerboards



Pack	Cat No.	Computer & Communications powerboards with surge protection and overload protection, 240V a.c.
5	D105PA4RJ	Teleguard™ telecommunications powerboard with 4 outlets, overload protection, 450J surge protection phone /data /modem / internet line, 10A, White, 1.8m lead
5	D105PA6RJ	Teleguard™ telecommunications powerboard with 6 outlets, overload protection, 450J surge protection phone /data / modem / internet line, 10A, White, 1.8m lead
5	D105PP4RJ	Computer powerboard with 4 outlets, 450J surge protection, RFI filtering on poweroutlets, and surge protected phone / data / modem / internet line 10A, White, 1.8m lead
5	D105PP6RJ	Computer powerboard with 6 outlets, 450J surge protection, RFI filtering on poweroutlets, and surge protected phone / data / modem / internet line 10A, White, 1.8m lead

## Heavy-duty powerboards



Pack	Cat No.	Plug Boss™ heavy duty powerboards, 240V a.c.
5	D105PB0SS5	5 outlet powerboard, spacing for up to 3 transformer plugs, 1.8m lead, 10A, cable management, "parking clip" plug, black

## Nursery plugs



Pack	Cat No.	Nursery Plugs
10	D1002	Child safety plug, 3 pin flat, pack of 6
10	D1002/1	Child safety plug, slimline, pack of 12

## Travel plugs



Pack	Cat No.	Travel plugs
5	D121	Available in White (WE) only. Pack of three plug adaptors to allow Australian appliances to be plugged into UK, European and US outlets
5	D121A	Adaptor to plug Australian appliances into US outlets
5	D121E	Adaptor to plug Australian appliances into European outlets
5	D121UK	Adaptor to plug Australian appliances into UK outlets
10	D122	Reverse adaptor allows European, Canadian or US appliances to be plugged into Australian outlets

## Lamp and light fittings



Pack	Cat No.	Fluorescent accessories
10	DF20	Fluorescent starters, 18 or 20W, pack of 2
10	DF40	Fluorescent starters, 4 to 65W, pack of 2



Pack	Cat No.	Globe grabber
5	D1004	Globe grabber, Fits onto broom handle to remove standard light globes



Pack	Cat No.	Canopy set and BC adaptor
5	D9500	Plug-in canopy light set with safety lampholder & 0.5m lead

## Moonglow night lights



Pack	Cat No.	Moonglow night lights
5	D1001/1	Moonglow nightlight
5	D1001/2	Moonglow nightlight, 'Happy Light' with happy face motif
5	D1001/4	Moonglow nightlight, 'Starlight' motif

## Connectors and terminal block



Pack	Cat No.	Connectors
10	D401	Single-screw connector with large 6mm hole and see-through body for safety checking. Rated 40 Amps. Pack of 10.
1	R401B	Single-screw connector with large 6mm hole and see-through body for safety checking. Rated 40 Amps. Box of 100.
10	D402	Two-screw connector with large 6mm hole and see-through body for safety checking. Rated 40 Amps. Pack of 10.
50	R402B	Two-screw connector with large 6mm hole and see-through body for safety checking. Rated 40 Amps. Box of 100.
10	D35P6	Terminal block connector strip, 6-way. White

## Fuse Wire



Pack	Cat No.	Fuse Wire
10	R1202	Fuse wire card with 8A and 16A fuse wire
10	D1202/16	Fuse wire reel, approx. 14 metres of 16A fuse wire
10	D1202/8	Fuse wire reel, approx. 55 metres of 8A fuse wire